# **Temperature Sensor**

## FXDD012 Part Number


- FDA compliant
- Response time T90: < 2 seconds
- Robust stainless steel housing with IP69K
- Temperature measuring range: -50 ... +200° C

### Technical Data

Sensor-specific data							
Sensor element	PT100, Class B						
Temperature Measurement Range	-50200 °C						
Medium	Liquids, gases						
Response Time	< 2 s						
Environmental conditions							
Temperature of medium	-50200 °C						
Ambient temperature	-2580 °C						
Storage temperature	-2580 °C						
Mechanical Strength	16 bar						
Shock Resistance	IEC 60751						
Vibration resistance	IEC 60751						
Mechanical Data							
Housing Material	1.4404						
Material in contact with media	1.4404						
Degree of Protection	IP68/IP69K *						
Connection	M12 × 1; 4-pin						
Process Connection	Varivent N						
Process Connection Length (PCL)	35,5 mm						
Probe Length (PL)	9,5 mm						
PT100							
Connection Diagram No.	140						
Suitable Connection Technology No.	21						
* Tested by wenglor							

\* Tested by wenglor


weFlux<sup>2</sup> Temperature Sensors ensure precise temperature measurement of liquids and gases in closed piping systems. It's easy to incorporate the standardized PT100/PT1000 resistance value into the controller. The compact housing with a diameter of just 27 mm is made of V4A stainless steel and features an easy-toclean surface. Thanks to their rugged housing and functional design, the Temperature Sensors are FDA compliant.




### weFlux<sup>2</sup> InoxSens

**Fluid Sensors** 





All dimensions in mm (1 mm = 0.03937 Inch)



Learned							
Legen		PŤ	Platinum measuring resistor	ENA	Encoder A		
+	Supply Voltage +	nc	not connected	ENв	Encoder B		
-	Supply Voltage 0 V	U	Test Input	Amin	Digital output MIN		
~	Supply Voltage (AC Voltage)	Ū	Test Input inverted	Амах	Digital output MAX		
А	Switching Output (NO)	W	Trigger Input	Аок	Digital output OK		
Ā	Switching Output (NC)	0	Analog Output	SY In	Synchronization In		
V	Contamination/Error Output (NO)	0-	Ground for the Analog Output	SY OUT	Synchronization OUT		
V	Contamination/Error Output (NC)	BZ	Block Discharge	OLT	Brightness output		
E	Input (analog or digital)	Awv	Valve Output	м	Maintenance		
т	Teach Input	а	Valve Control Output +				
Z	Time Delay (activation)	b	Valve Control Output 0 V				
S	Shielding	SY	Synchronization	Wire Colors according to DIN IEC 757			
RxD	Interface Receive Path	E+	Receiver-Line				
TxD	Interface Send Path	S+	Emitter-Line	BK	Black		
RDY	Ready	÷	Grounding	BN	Brown		
GND	Ground	SnR	Switching Distance Reduction	RD	Red		
CL	Clock	Rx+/-	Ethernet Receive Path	OG	Orange		
E/A	Output/Input programmable	Tx+/-	Ethernet Send Path	YE	Yellow		
۲	IO-Link	Bus	Interfaces-Bus A(+)/B(-)	GN	Green		
PoE	Power over Ethernet	La	Emitted Light disengageable	BU	Blue		
IN	Safety Input	Mag	Magnet activation	VT	Violet		
OSSD	Safety Output	RES	Input confirmation	GY	Grey		
Signal	Signal Output	EDM	Contactor Monitoring	WH	White		
BI_D+/-	Ethernet Gigabit bidirect. data line (A-D)	ENARS422	Encoder A/Ā (TTL)	PK	Pink		
	Encoder 0-pulse 0-0 (TTL)		Encoder B/B (TTL)	GNYE	Green/Yellow		

